

PICKING STATION WITH WORKSTATION - CAPACITY: 36 SPECIALITIES

Description

MOBILE PICKING STATION WITH 2 RAILS - WORKSTATION - WALL-MOUNTED
DRAWER UNIT F600 6G - 18 CLEAR LABEL HOLDERS 1/4 - INCLUDING PICKING
STATION: 18 DRAWER DIVIDER BINS 075 1/4 (36 MOBILE SEPARATORS) -

WEIGHT

Weight bare structure	50 kg
Total Weight - Pack	67 kg

DIMENSIONS

Width	139,4 cm
Depth	52 cm
Height	191 cm



PACK - EQUIPMENT

Composition 2 rails - 18 label holder 1/4 - 18 drawers dividers bin 075
1/4 (36 mobile separators) - 3 white drawers height 155

WEIGHT

Weight bare structure 50 kg
Total Weight - Pack 67 kg

DIMENSIONS

Width 139,4 cm
Depth 52 cm
Facade F600
Height 191 cm
Thickness 1,3 cm

TYPE

Type of brake Individual brake

MATERIAL & COATING

Frame Welded steel - Volcanic Black Epoxy
Box Monobloc structure - Welded steel
Top Compact HPL
Wheels Thermoplastic rubber, grey non-marking

BASE

Type of footing 4 swivel wheels with 2 braked at the front
Wheels diameter 125 mm

CONFIGURATION

Configuration Workstation - Wall-mounted Drawer Unit F600 6G

COLORS

Box Colors to choose from in our selection

CAPACITY

P20 6G
Drawer height 75 mm 6
ABS tray height 50 mm 6
Shelf for Daily pillboxes medium model height 50 mm 8

FIRE CLASSIFICATION

Compact HPL M1

FIRE CLASSIFICATION

Plastic M2